



Pre-measurement Peak List

| Trace | Frequency | Level      | Limit      | Delta Limit | Delta Ref | Comment |
|-------|-----------|------------|------------|-------------|-----------|---------|
| 1 PK+ | 535 kHz   | 65.85 dBµV | 70.00 dBµV | -4.11 dB    |           |         |
| 2 AV  | 535 kHz   | 57.84 dBµV | 50.00 dBµV | 7.84 dB     |           |         |
| 1 PK+ | 595 kHz   | 75.57 dBµV | 70.00 dBµV | 5.57 dB     |           |         |
| 2 AV  | 595 kHz   | 65.45 dBµV | 50.00 dBµV | 19.45 dB    |           |         |
| 2 AV  | 710 kHz   | 55.30 dBµV | 50.00 dBµV | 5.30 dB     |           |         |
| 1 PK+ | 730 kHz   | 67.81 dBµV | 70.00 dBµV | -2.99 dB    |           |         |
| 2 AV  | 905 kHz   | 48.22 dBµV | 50.00 dBµV | -1.78 dB    |           |         |
| 2 AV  | 1.095 MHz | 45.09 dBµV | 50.00 dBµV | -4.91 dB    |           |         |
| 2 AV  | 1.445 MHz | 49.82 dBµV | 50.00 dBµV | -0.17 dB    |           |         |
| 2 AV  | 1.72 MHz  | 46.63 dBµV | 50.00 dBµV | -3.37 dB    |           |         |