

Model EME-G634A

File Number: E41429



COMPANY

SUMITOMO BAKELITE CO LTD
5-8 HIGASHI-SHINAGAWA 2-CHOME
SHINAGAWA-KU, Tokyo 140-0002 Japan

MODEL INFO

EME-G634A
Epoxy Molding Resin (EP - Molding) "SUMIKON", furnished as tablet, powder, or granule

FLAMMABILITY PROPERTIES	VALUE	TEST METHOD
Flammability (3.0 to 3.3 mm, Color: BK)	V-0	ANSI/UL 94
ISO/IEC FLAMMABILITY PROPERTIES	VALUE	TEST METHOD
Flammability (3.0 to 3.3 mm, Color: BK)	V-0	IEC 60695-11-10
THERMAL PROPERTIES	VALUE	TEST METHOD
Relative Thermal Index - Electrical Strength (3.0 to 3.3 mm)	130 °C	UL 746B
Relative Thermal Index - Mechanical Impact (3.0 to 3.3 mm)	130 °C	UL 746B
Relative Thermal Index - Mechanical Strength (3.0 to 3.3 mm)	130 °C	UL 746B

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL Solutions' Follow - Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL Solutions' Follow - Up Service. Always look for the Mark on the product.

UL Solutions permits the reproduction of the material contained in Product iQ subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from Product iQ with permission from UL Solutions" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "©2025 UL LLC."