


INPUT 10~40V
 LED VF=3.5V
 I LED=0.55A
 FSW=250KHZ
 INPUT UVLO=9V
 VHYS=2V
 OUTPUT OVLO=70
 VHYSO=30V

TITLE:			
Doc. File Name: 3-3751.Sch			
Date: 25-Jan-2017	Sheet: 0 of 0	Edit By:	