


VIN: 70V
 VOUT: 17V
 IOUT: 1.3A (Electronic load CC mode)


●Normal waveform



1CH(Blue): HighSide FET 100us/div
 2CH(Light Blue): Inductor current


*HighSide FET is measured on the source side with the drain grounded.

Expansion



1CH(Blue): HighSide FET 10us/div
 2CH(Light Blue): Inductor current

●Abnormal waveform



1CH(Blue): HighSide FET 10us/div
 2CH(Light Blue): Inductor current