

Vin:10V
Vout:6.5V
Iout:1A
Fsw:400kHz



Vin:9.9V
Vout:6.5V
Iout:1A
Fsw:400kHz



Vin:6.8V
Vout:6.5V
Iout:1A
Fsw:400kHz



Vin:5V
Vout:6.5V
Iout:1A
Fsw:400kHz

