

Vin	No Load	2A Load	5A Load	20V Load	18V Load	15V Load	10V Load	5V Load
50V	20.59V	20.48V	20.33V	5.58A	5.58A	5.58A	5.58A	5.6A
40V	20.58V	20.48V	20.32V	5.55A	5.55A	5.55A	5.56A	5.57A
30V	20.57V	20.47V	20.31V	5.55A	5.55A	5.55A	5.55A	5.55A
25V	20.57V	20.47V	20.31V	5.54A	5.54A	5.54A	5.54A	5.54A
23V	20.15V	19.71V	19.43V	1.6-2.8A	5.52A	5.53A	5.53A	5.53A
22V	20.07V	19.8V	19.5V	0.61A	5.51A	5.51A	5.52A	5.53A
21V	20.19V	19.82V	19.5V	0.83A	5.5A	5.52A	5.52A	5.52A
20V	20.3V	19.91V	19.55V	1.65A	5.45A	5.51A	5.52A	5.52A
19V	19.86V	19.71V	19.58V	0A	5.45A	5.5A	5.51A	5.52A
18V	19.75V	19.5V	18.84V	0A	5.39A	5.5A	5.51A	5.52A
15V	20.34V	19.74V	18.95V	1.23A	5.35A	5.4A	5.5A	5.51A
13V	20.57V	20.01V	19.27V	1.98A	5.32A	5.44A	5.33A	5.5A
11V	19.94V	20.05V	19.19V	0A	5.29A	5.32A	5.38A	5.5A
10V	17.98V	18.6V	19.05V	0A	0A	5.34A	5.4A	5.5A

0V Load
5.45A
5.47A
5.48A
5.47A
5.45A
5.44A
5.44A
5.42A
5.42A
5.42A
5.39A
5.36A
5.33A
5.32A