


Lab Notebook Entry from LeCroy DSO
DSO S/N: LCRY0604P14011
User: LeCroyUser
Time: 2/20/2004 2:12:44 AM

2/20/2004 2:12:44 AM



Channel Status

	C1	C3	C4
Vertical	V / Div	2.00 V	5.00 V
	Offset	-6.000 V	-15.00 V
	Coupling	DC1M Ω	DC50 Ω
	BW-Limit	Full	Full
	Probe	10	1.000000
	Sweeps	---	---

Acquisition Status

Time / Div 500 ns Sampling Rate 5.0 GS/s

Horizontal	Time / Pt	200 ps	Sampling Mode	RealTime
	Pts / Div	2.5000 kS	Trigger Delay	-10 ns
	Mode	Stop	Slope	Positive
Trigger	Type	Edge	Level	540 mV
	Source	C4	Coupling	DC