



0 V
4.00 μ s
250MS/s
1
/
187.6000 μ s
10k points
3.20 V

	Value	Mean	Min	Max	Std Dev
	3.12 V	3.12	3.12	3.12	0.00
Frequency	6.154MHz	6.154M	6.154M	6.154M	0.000
	4.04 V	4.04	4.04	4.04	0.00