



0 V

10.0μs      100MS/s      1 / f  
→ 187.5000μs      10k points      3.20 V

	Value	Mean	Min	Max	Std Dev
Amplitude	785mV	817m	785m	849m	26.3m
Frequency	8.743MHz	Low resolution			
Level	4.30 V	4.40	4.30	4.50	115m

Save Waveform    Save Setup    Recall Waveform    Recall Setup    Assign **Save** to **Waveform**