



0 V

20.0ms 50.0kS/s 1 /
 0.000000 s 10k points 1.20 V

	Value	Mean	Min	Max	Std Dev
Frequency	14.9 V	12.5	-6.13m	14.9	3.46
	7.143kHz	Low resolution			
	15.3 V	13.7	300m	15.5	2.75

Save Waveform Save Setup Recall Waveform Recall Setup Assign Save to Waveform