

P1VB_AUX SPECIFICATION

VOUT=1.8V
RIPPLE<30mV
DC TOL=TBD
TOTAL TOL=+/-90mV (+/-5%)
IOUT TDC=2.25A
IOUT MAX=TBD
LOAD RATE=TBD
SLEW RATE=TBD
WORK FREQUENCY=600KHZ
EFFICIENCY > 90%
OCP(IOUT MAX *1.62)=3.65A(TYP)
VIN UULO<RISING/FALLING=2.4V/1.85V
VOUT OUP/UVP=2.05V/1.44V

P1VB_AUX

