


REVISION RECORD			
LTR	ECO NO:	APPROVED:	DATE:

REVISION HISTORY


REV V1.0 :

initialization Version








		COMPANY: REVISION_HISTORY									
		TITLE:									
DRAWN: hedongqiang		DATED: 2011.05.06									
CHECKED: System Team		DATED: 2011.05.06									
QUALITY CONTROL:		DATED:									
RELEASED:		DATED:		CODE:		SIZE:		DRAWING NO:		REV:	
SCALE:				SHEET: OF							

REVISION RECORD			
LTR	ECO NO:	APPROVED:	DATE:





Note:
The 24VAC input source must be electrically isolated from Earth by 1500 VAC per IEEE 802.3-2005 Cat1-2006. Ports that connect across ground zones have special isolation requirements. Any noise from the 24VAC source must not corrupt Ethernet data.



DRAWN:	hedongqiang	DATED:	
CHECKED:	System Team	DATED:	
QUALITY CONTROL:		DATED:	
RELEASED:		DATED:	





COMPANY:			
TITLE:			
CODE:	SIZE:	DRAWING NO:	REV:
SCALE:		SHEET OF	

REVISION RECORD			
LTR	ECO NO.	APPROVED.	DATE.









DRAWN: hedongqiang		DATED:		COMPANY:			
CHECKED: System Team		DATED:		TITLE:			
QUALITY CONTROL:		DATED:		CODE:	SIZE:	DRAWING NO:	REV:
RELEASED:		DATED:		SCALE:			SHEET: OF

REVISION RECORD			
LTR	ECO NO.	APPROVED	DATE




RS485



ALARM

M1 M2 M3 M4
FIDUCIAL FIDUCIAL FIDUCIAL FIDUCIAL



○ 90 OHM
⊗ 90 OHM
△ 90 OHM
90 OHM

DRAWN:	hedongqiang	DATED:	
CHECKED:	System Team	DATED:	
QUALITY CONTROL:		DATED:	
RELEASED:		DATED:	

COMPANY:			
TITLE:			
CODE:	SIZE:	DRAWING NO:	REV:
SCALE:			SHEET OF