



	Cursor 1	Cursor 2	Delta C2-C1
Frequency	1 MHz	10 MHz	9 MHz
Trace 1	Magnitude (dB)	Magnitude (dB)	Magnitude (dB)
Measurement	56.862 dB	19.149 dB	-37.713 dB

Sweep	
Start frequency:	10 Hz
Stop frequency:	10 MHz
Center frequency:	5 MHz
Span:	10 MHz
Sweep mode:	Logarithmic
Numer of points:	201

Calibration	Full-Range	User-Range
Gain	-	-

Termination	Channel 1	Channel 2
Gain	1 M Ω	50 Ω

Attenuator setting	Channel 1	Channel 2
Transmission	20 dB	20 dB

Hardware setup	
Device type:	Bode100R2
Serial number:	PC200H
Receiver bandwidth:	30 Hz
Output level:	100 mVpp
DUT settling time:	100 ms