



	Cursor 1	Cursor 2	Delta C2-C1
Frequency	464.159 Hz	21.544 kHz	21.08 kHz
Trace 1	Magnitude (dB)	Magnitude (dB)	Magnitude (dB)
Measurement	83.408 dB	70.49 dB	-12.918 dB

Sweep	
Start frequency:	10 Hz
Stop frequency:	10 MHz
Center frequency:	5 MHz
Span:	10 MHz
Sweep mode:	Logarithmic
Numer of points:	401

Calibration	Full-Range	User-Range
Gain	-	-

Termination	Channel 1	Channel 2
Gain	1 MΩ	1 MΩ

Attenuator setting	Channel 1	Channel 2
Transmission	0 dB	0 dB

Hardware setup	
Device type:	Bode100R2
Serial number:	PC200H
Receiver bandwidth:	10 Hz
Output level:	100 mVpp
DUT settling time:	50 ms