

## Connected to a 5V / 1.5A Source

### Received Source Capabilities ( 0x30 )

Number of Source PDOs

1

Source PDO 1

Field	Value
Maximum Current	1.5 A
Voltage	5 V
Peak Current	130%
Unchunked Extended Msg Supported	True
USB Capable	True
USB Suspend Supported	True
Dual Role Data	True
Externally Powered	False
Dual Role Power	True
Supply Type	Fixed Source

### Active Contract PDO ( 0x34 )

Field	Value
Maximum Current	1.5 A
Voltage	5 V
Peak Current	130%
Supply Type	Fixed Source

### Active Contract RDO ( 0x35 )

Field	Value
Max/Min Operating Current	3 A
Operating Current	1.5 A
No USB Suspend	True
USB Communication Capable	True
Capability Mismatch	True
Giveback Flag	False
Object Position	1

## Connected to a 5V / 1.5A Source

### Received Source Capabilities ( 0x30 )

Number of Source PDOs

1

Source PDO 1

Field	Value
Maximum Current	3 A
Voltage	5 V
Peak Current	100%
Unchunked Extended Msg Supported	True
USB Capable	True
USB Suspend Supported	False
Dual Role Data	False
Externally Powered	False
Dual Role Power	False
Supply Type	Fixed Source

### Active Contract PDO ( 0x34 )

Field	Value
Maximum Current	3 A
Voltage	5 V
Peak Current	100%
Supply Type	Fixed Source

### Active Contract RDO ( 0x35 )

Field	Value
Max/Min Operating Current	3 A
Operating Current	3 A
No USB Suspend	True
USB Communication Capable	True
Capability Mismatch	False
Giveback Flag	False
Object Position	1