



4.00ms 250kS/s 1 / 3.20 V
 188.0000µs 10k points

0 V

	Value	Mean	Min	Max	Std Dev
Amplitude	719mV	719m	717m	721m	1.22m
Frequency	103.5 Hz	103.3	103.1	103.5	91.57m
Level	3.82 V	3.80	3.78	3.82	20.0m

Save Waveform
Save Setup
Recall Waveform
Recall Setup
Assign **Save** to **Waveform**