

bqStudio Version: 1.3.86



EV2400
Version:0.18



SMB
bq78350_R1
1e9b_1_03
Addr: 0x17
25.1 degC

Registers

Registers

Start Log Scan Refresh

Registers

Name	Val...	U...	Name	Val...	U...	Name	Val...	U...	Name	Val...	U...	Name	Val...	U...	Name	Val...	U...
⌕Manufactur...	0x...	h...	⌕At Rate Tim...	65...	n...	⌕Average Cu...	0	n...	⌕Full charge ...	9920	n...	⌕Charging V...	0	n...	⌕Cell 2 Voltage	3323	n...
⌕Remaining ...	1100	n...	⌕At Rate OK	1	-	⌕Max Error	100	%	⌕Run time To...	65...	n...	⌕Cycle Count	65...	-	⌕Cell 3 Voltage	3326	n...
⌕Remaining ...	10	n...	⌕Temperature	25.1	d...	⌕Relative St...	90	%	⌕Average Ti...	65...	n...	⌕Pending EDV	3060	n...	⌕Cell 4 Voltage	3326	n...
⌕At Rate	0	n...	⌕Voltage	5010	n...	⌕Absolute St...	65535	%	⌕Average Ti...	65...	n...	⌕State of He...	99	%	⌕Cell 5 Voltage	3327	n...
⌕At Rate Tim...	65...	n...	⌕Current	0	n...	⌕Remaining ...	8865	%	⌕Charging C...	0	n...	⌕Cell 1 Voltage	3326	n...	⌕Cell 6 Voltage	3334	n...
															⌕Cell 7 Voltage	3330	n...
															⌕Cell 8 Voltage	3463	n...
															⌕Cell 9 Voltage	3334	n...
															⌕Cell 10 Volt...	3333	n...
															⌕Cell 11 Volt...	3331	n...
															⌕Cell 12 Volt...	3334	n...
															⌕Cell 13 Volt...	3335	n...
															⌕Cell 14 Volt...	3334	n...
															⌕Cell 15 Volt...	3336	n...
															⌕Ext Avg Cell...	3338	n...
															⌕TS1 Temper...	24.8	d...
															⌕TS2 Temper...	25.0	d...
															⌕TS3 Temper...	25.1	d...
															⌕Cell Temper...	25.1	d...
															⌕FET Tempe...	-27...	d...
															⌕Gauge Inter...	25.0	d...

Bit Registers

Bit High Bit Low RSVD

[illegible]