

## 2K resistors into TL1451 pin 3


Channel 1 LM6144 Pin 8

Channel 2: TL1451 pin 3


Channel 3 LM6144 pin 9

Channel 4: LM6144 pin 10

1: -60C 3.3Vout load (no start)



2: -60C 50mA load



Inputs get pulled apart when no start happens