

FAN_IN_12V

C113

0.1uF/25V

[7]

EN_FAN1

R154
*4.7K

C111
*56pF

C115
*56pF

R151
86.6

L19
*100MHz/6A/30ohm

L18
100MHz/6A/30ohm

NRETRY_FAN1

RT_DELAY_FAN1

ILIM_FAN1

VCC CL Fan1

IN1

IN2

IN3

IN4

P1

1

2

3

16

PAD1

12

LDSTRT

6

EN/UVP

11

NRETRY

10

RETRY_DELAY

8

ILIM

U18

GND1

GND2

14

GND3

P2

4

5

14

P2

TPS25982x

OUT8

OUT7

OUT6

OUT5

OUT4

OUT3

OUT2

OUT1

PG

IMON

DVDT

ITIMER

24

23

22

21

20

19

18

17

13

9

15

7

FAN_IN_3V3

R150

100K

C114
*4.7nF

C112
3300pF

R152
4.7K

C110
0.1uF/25V

C109
10uF/25V

C108
22uF/25V

VCC 12P Fan1