



PARAMETER	TEST CONDITION	MIN	TYP	MAX	UNIT
VDDQ MOSFET DRIVER					
R_{DRVH}	DRVH resistance	Source, $I_{DRVH} = -50$ mA	1.6	3.0	Ω
		Sink, $I_{DRVH} = 50$ mA	0.6	1.5	
R_{DRVL}	DRVL resistance	Source, $I_{DRVL} = -50$ mA	0.9	2.0	Ω
		Sink, $I_{DRVL} = 50$ mA	0.5	1.2	

