

2.00 V/div

1.00 V/div

Main : 125 k

1us/div



Max(C2) 5.49 V  
Max(C3) 5.58 V

Min(C2) 4.47 V  
Min(C3) -0.82 V

Rms(C2) 5.01197 V  
Rms(C3) 4.19117 V