



29.01.2018 14:13:56

Canal	Nom	Échelle	Valeur	Min.	Max.	Moyenne	Écart-type
A	Maximum	Tracé complet	5.969 V	5.969 V	5.969 V	5.969 V	0 V
B	Maximum	Tracé complet	1.875 V	1.875 V	1.875 V	1.875 V	0 V