

Min	TY P	MA X
2.2		5.5
1.8		5.2
-1.5%		+1.5%
-1.5%		3.5%
Yes		
		meet
		meet
		meet
		meet
		meet
meet		
-0.3		6
-3		9
		meet
		meet
		meet
		NA
		meet
		meet
		meet
		meet
		meet
		Has OCP
		Has OTP
		meet

		<i>Support 100k/40 0k/1Mhz I2C</i>
<i>Support Power cycle and toggling EN pin to reset Regs</i>		
<i>Support I2C address</i>		
HBM 2kV		
CDM 500V		
±100mA		
NA		
0.4fit		
Follow JEDEC		
Follow JEDEC		
Follow JEDEC		
Follow JEDEC		
NA		
NA		
Follow JEDEC		
Package level quarterly monitor		
Yes		
NA		
Yes		
NA		
Yes		
Yes		
Yes		
Yes		
Yes		
Ta: -40～85度		
Tj: -40～125度		
-55～150度		
UL94		
meet		
meet		
2.3*1.4mm		
1		

