

	TPS563209	TPS563209	TPS54327	TPS54327
Vin(V)	12	12	12	12
Vout(V)	1.5	1.5	1.5	1.5
Iout(A)	3	3	3	3
Ta(°C)	27	50	27	50
Tc(°C)	74	100	53	75
Power Dissipation(W)	0.84	0.92	1.21	1.22
Tj(°C)	76.6	102.8	59.1	81.1
Air	No	No	No	No