





input 100 V
 output 12 V
 27 A

OK_IC



	Scale	Bw
CH1	2 V/div	20MHz
CH2	10 V/div	20MHz
CH3	2 V/div	20MHz
CH4	2 V/div	20MHz
REF1	-	-
REF2	-	-
REF3	-	-
REF4	-	-
MATH	-	-

TIME	40 ms/div
Mode	SAMPLE




input
output

NG_IC


100 V
12 V
27 A

IC_5pin
IC_3pin
IC_14pin
Vgs




	Scale	Bw
CH1	2 V/div	20Mhz
CH2	10 V/div	20Mhz
CH3	2 V/div	20Mhz
CH4	2 V/div	20Mhz
REF1	-	-
REF2	-	-
REF3	-	-
REF4	-	-
MATH	-	-


TIME	40 ms/div
Mode	SAMPLE



TIME	4 us/div
Mode	SAMPLE



TIME	4 us/div
Mode	SAMPLE



TIME	4 us/div
Mode	SAMPLE