

VIN=15.8V

v: 20.527 V

Δv : 5.079 V

v: 15.448 V

C1: Voltage across Drain and source of the low-side mosfet (SW)

C2: HDRV

C3: LDRV

DVM
DC+AC RMS
8.719 mV
Meas 1
Mean
 μ : 9.786 V
Meas 4
Frequency
 μ : ...
Too few edges

Ch 1 5 V/div 10 V/div 500 MHz 500 MHz
Ch 2 2 V/div 500 MHz
Ch 3 2 V/div 500 MHz
Math 1 2 V/div Ch1 - Ch2
Math 2 50 Ohms/div Ch2 / Math1
Bus 1 RS-232
4
Add New Math Add New Bus
Horizontal 40 ns/div 400 ns SR: 6.25 GS/s RL: 2.5 kpts
Trigger 20.2 V
Acquisition Auto, Sample: 8 bits, 0 Acqs
Preview 01 Jun 2022 11:10:53 AM

Add New...
Cursors Callout
Measure Search
Results Table Plot
More...

