


DC REGULATED

10E

599





GW INSTEK GDS-1022



VARIABLE

CH 1

VOLTS/DIV

Auto  

Vpp
1: 2.40V
2: chan off


Vavg
1: 492mV
2: chan off

Frequency
1: ?
2: chan off

Duty Cycle
1: ?
2: chan off

Rise Time
1: ?
2: chan off

GW INSTEK



0 5V
2 50mV

250ns Roll

CH1 EDGE FDC

GW INSTEK GDS-1022

Digital Storage Oscilloscope
25MHz 250M Samples

GW INSTEK

Auto

Measure



V = 5V

250ms/div

CH1


EDGE

FDC

200Hz

GW INSTEK GDS-1022

Display Storage Oscilloscope
200MHz, 200M Sa/s



GW INSTEK GDS-1022

Signal Source: Channel 1
Time: 200ns

ON/OFF AUTO/MAN HOLD


12.73

RISH CLAMP 300A





ON/OFF HOLD AUTO/MAN




RISH Clamp 300A



RISHABH




AUTOMATIC HOLD ON/OFF



RISHI 3004





ALTOHMAN HOLD ONOFF



FRISH Quantity 300A

