

R10=610k Ω
R17=130k Ω
C18=1000pF
R12=3.9k Ω
R13=3.9k Ω
C25=0.047 μ F
R22=100k Ω
C1=0.1 μ F
C2+C3=22 μ F
R14=150k Ω
C29=Non
C32=Non
R15=10k Ω
L1=4.7 μ H
C21=22 μ F
C7,8,9,10=Non
C4=33 μ F x 2
R26=0 Ω
R27=0 Ω
R40=Non
CMPIN=Connect to GND
R34=24k Ω //100pF
R33=Non
R35=3k Ω
R36=3k Ω
R43,D3=Non
R45,D5=Non