



0 V

4.00ms 250kS/s 1 /

188.0000µs 10k points 3.20 V

	Value	Mean	Min	Max	Std Dev
Amplitude	165mV	165m	165m	165m	0.00
Frequency	103.4 Hz	103.4	103.4	103.4	0.000
Level	1.94 V	1.94	1.94	1.94	0.00

Save Waveform Save Setup Recall Waveform Recall Setup Assign Save to Waveform