



Add New...

Cursors Callout Search Plot More...

Measure Results Table

DVM DC+AC RMS **3.749 mV**

Meas 1 Mean μ : 1.552 V

Meas 4 Frequency μ : 1.263 MHz

Horizontal 400 μ s/div 4 ms SR 312.5 MS/s 3.2 ns/pt RL 1.25 Mpts 10.9%

Trigger 4 A

Acquisition Auto Analyze Sample: 12 bits 0 Acqs

Preview 01 Jun 2022 9:16:50 AM

Ch 1 5 V/div 500 MHz Ch1 - Ch2

Ch 2 5 V/div 500 MHz

Math 1 2 V/div Ch1 - Ch2

Math 2 50 Ohms/div Ch2 / Math1

Bus 1 RS-232

3 4