




# RS232



Note1:  $V_{OUT} = (R1 + R2) / R2 \times 1.207$



|         |   |
|---------|---|
| OPEN    | 3 |
| UAR_RDO | 4 |
| UAR_XDO | 5 |
| GND     | 2 |
| OPEN    | 1 |