



1



R128 R122 R129  
 16s 0 open open  
 12s open 0 open R60~R63:open C19~C22: 0Ω  
 7s open open 0 R60~R68:open C19~C27: 0Ω  
 その他の段数の時は16sの設定で  
 CN6のpin20に最高電位をいれる。

2



pin	Cell
1	V0
2	V0
3	V1
4	V2
5	V3
6	V4
7	V5
8	V6
9	V6
10	V7
11	V8
12	V9
13	V9
14	V10
15	V11
16	V12
17	V13
18	V14
19	V15
20	V16

3

