


VCC 1.8V VOLTAGE GENERATION



+V1.8A	
CURRENT LIMIT (TYP) A	4
SWITCHING FREQUENCY (KHz)	1000
OUTPUT VOLTAGE (V)	1.8
LOAD CURRENT (A)	2.8
IRMS (MAX) A	4
ISAT (MAX) A	4.5

Title	
<Title>	
Size	Document Number
A3	<Doc>
Date:	Monday, October 07, 2024
Sheet	1 of 1

Rev
<Rev Code>