

VOUT -722.8mV



I1 = 10m
 I2 = 1.25
 TD = 7m
 TR = 10u
 TF = 10u
 PW = 500u
 PER = 1m

Schematic is same as previous one, I just changed the delay time.

ΔI_{OUT_TRA} (A)	C_{OUT} (F)	C_{FF} (F)	F_{SW} (Hz)
1,25 A(10m – 1,25)	12u	180p	400k

STARTUP AND TRACKING

t_{SS} Internal soft-start time 4.2 ms



Yellow would be expected behaviour, but this red one before output loading starts is my concern.