


Title		
Size	Number	Revision
A3		
Date:	10.05.2023	Sheet of
File:	G:\Drugi računalniki\Schematic\02.Sch	Down By:



44 57



44

44

44



57

44



Comment	Description	Designator	Footprint	LibRef	Quantity
Generic Capacitor model		C1, C2, C3, C4, C5, C6, C7, C8, C9, C10, C11, C18, C19, C20, C21, C22, C23, C24, C25, C26, C27, C28, C29, C30	CAP_0603	Cap	24
Cap_Polarized	Generic polarized cap symbol	C12, C13, C14, C15	CAP_SMD_10X10.2	Cap_Polarized	4
Generic Capacitor model		C16, C17	Cap_0805	Cap	2
MBR0580S1-7	DIODE SCHOTTKY 80V 500MA SOD123	D1, D2	MBR0580S1-7	MBR0580S1-7	2
Diode LED Green	Generic green LED symbol	D3, D4	DIODE_0603	Diode LED Green	2
Diode LED Red	Generic red LED symbol	D5, D6, D7	DIODE_0603	Diode LED Red	3
Diode LED Blue	Generic blue LED symbol	D8	DIODE_0603	Diode LED Blue	1
DRV8306	TI, BLDC Motor Controller	IC1	VQFN (32) 4x4	DRV8306	1
Nmos	Generic Nmos symbol.	Q1, Q2, Q3, Q4, Q5, Q6	POWERPAK SO-8	Nmos	6
Generic resistor model		R1, R2, R3, R4, R5, R6, R7, R8, R9, R10, R11, R12, R13, R14, R15, R16, R17, R18, R19, R20, R21, R22, R23, R24, R25, R26, R27, R28, R29, R31, R32, R33, R34, R35, R36, R38, R39, R40, R41, R42	RES_0603	Res	40
Y14780R00050F9R	Shunt 500uR	R30	Y14780R00050F9R	Y14780R00050F9R	1
3314J-1-253E	TrimPot 25k, 1 turn, SMD	R37	3314J-1-253E	3314J-1-253E	1
OS102011MA1QS1	Switch slide, THT, right-angle, 100mA	SW1, SW2, SW3, SW4	OS102011MA1QS1	OS102011MA1QS1	4
Jumper 2.54mm	Jumper 2.54mm	X1		Jumper 2.54mm	1
Pin Header 2x6, 2.54mm, THT, Straight	Pin Header 2x6, 2.54mm, THT, Straight	X2	PIN HEADER THT 2X6 2.54MM	Pin Header 2x6, 2.54mm, THT, Straight	1
Connector 10	Generic connector symbol, 10 positions	X3		Connector 10	1
PCB Terminal Spade	Spade PCB Terminal 6.35x0.81mm	X4, X5, X6, X7, X8	PCB Terminal SPADE	PCB Terminal Spade	5
A1502WR-S-6P	Pin header, 1x6, 1.5mm, SMT Right-angle	X9	A1502WR-S-6P	A1502WR-S-6P	1
TLC555CDR	Timer 555	X10	SOIC8	TLC555CDR	1