

Brushless DC-Servomotors 1628 2036 2444 3056 3564 4490

Digital hall sensor information

Characteristics	Value	Units
Supply Voltage	4.5 to 24	Vdc
Supply Current, typical	4	mA
Supply Current, max	8.7	mA
Sinking Output, max*	10	mA
Output Voltage, max	0.4	V
Frequency Range	up to 100	Khz

*open collector

