



Stack Size Models	RP34-112 / RP34M-79
Cont Stall Torque oz-in (Ncm)	112 (79)
Peak Torque oz-in (Ncm)	392 (277)
No Load Speed RPM	7000
Inertia oz-in-sec <sup>2</sup> (g-cm <sup>2</sup> )	0.0149 (1053.4)
Motor Weight oz (kg)	64 (1.79)
Poles	4

Step 3:	
Imperial	112V24
Metric	79V24
Voltage (Vdc)	24
Voltage Constant V/kRPM	3.4
Torque Constant oz-in/A (Ncm/A)	4.6 (3.2)
Max Cont Current (A)	24.4
Peak Current (A)	85.2