



HYBRID STEPPING MOTOR MOD. 42BYGHW248A-01

Wiring Diagram:



Dimensions:
(unit=mm)



Electrical Specifications

STEP ANGLE	1.8 ° /STEP	COMMENT
RATED VOLTAGE	12 V	
CURRENT	0.3 A/PHASE	
RESISTANCE	40 ± 10% Ω /PHASE	
INDUCTANCE	23 ± 20% mH/PHASE	
HOLDING TORQUE	1.57 kg. cm	
INSULATION CLASS	B	
DETENT TORQUE	115g. cm	

					<h2>42BYGHW248A-01</h2> <h3>技术条件</h3>	东莞一能机电技术
更改	数量	更改单号	签名	日期		
拟制						
审核						
批准						