

样品编号: 170744
 Sample ID:
 客户名: H612
 Customer:
 测试电压: DC 6V
 Test Voltage:
 旋转方向: CW/CCW
 Rotation Direction:
 制作日期: 2017.09.13
 Test Date:

承认 Approve	审核 Review	作成 Engineer
<i>杨智祥</i>	/	乐林

负载转矩:
 Rated Torque: 720g.cm

项目 Item 序号 No.	空载电流 Idle Current	空载转速 Idle Speed	空载噪音 Idle Noise	负载电流 Rated Current	负载转速 Rated Speed
	mA	RPM	Db	mA	RPM
1	312	150	32	673	142
2	350	149	34	633	140
3	340	149	49	654	142
4	333	152	42	648	143
5	287	150	32	660	141
MAX	350	152	49	660	143
MIN	287	149	32	633	140
X	324	150	39	649	142
备注 Remark	噪音测试方法: 探头距减速器100cm, 环境噪音32dB。 Test condition: Detector to gearbox at 100cm, in ambient noise at 32dB.				

