

11:10:07 APR 24, 2019

REF -10.0 dBm #ATTEN 0 dB

MKR Δ -203 kHz
-27.24 dB

PEAK
LOG
10
dB/

V A S B
S C F C
C O R R

MARKER Δ
-203 kHz
-27.24 dB

CH Φ

CENTER 1.042605 GHz
#RES BW 30 kHz

#VBW 30 kHz

SPAN 3.000 MHz
SWP 20 msec

Register Menu for COM97

Save Options Local Remote Address -> FFFFFFFF Read All Save Radio Settings Reset Help

Xcvt System Status Serial Neighbor Special Debug Engr LMX OFDM Test

R0	R	W	0003	R16	R	W	0000	R32	R	W	0000
R1	R	W	0010	R17	R	W	0000	R33	R	W	0000
R2	R	W	07E0	R18	R	W	0000	R34	R	W	1000
R3	R	W	0000	R19	R	W	0000	R35	R	W	0640
R4	R	W	1019	R20	R	W	0028	R39	R	W	11F1
R5	R	W	0101	R21	R	W	0101	R40	R	W	101C
R6	R	W	8184	R22	R	W	8584	R41	R	W	0810
R7	R	W	1084	R23	R	W	10A4	R42	R	W	0210
R8	R	W	000A	R24	R	W	0010	R47	R	W	0000
R9	R	W	0000	R25	R	W	0000	R53	R	W	7806
R10	R	W	0000	R26	R	W	0000	R58	R	W	8C00
R11	R	W	0000	R27	R	W	0000	R60	R	W	A000
R12	R	W	0000	R28	R	W	0000				
R13	R	W	0000	R29	R	W	0000				
R14	R	W	0000	R30	R	W	0000				
R15	R	W	0000	R31	R	W	0000				

CHØ

11:21:13 APR 24, 2019

REF -10.0 dBm #ATTEN 0 dB

MKR 1.046702 GHz
-10.69 dBm

PEAK
LOG
10
dB/

MARKER
1.046702 GHz
-10.69 dBm

VA SB
SC FC
CORR

CH16

CENTER 1.046710 GHz
#RES BW 30 kHz

#VBW 30 kHz

SPAN 3.000 MHz
SWP 20 msec

Register Menu for COM97

Save Options Local Remote Address-> FFFFFFFF Read All Save Radio Settings Reset Help

Xcvt System Status Serial Neighbor Special Debug Engr LMX OFDM Test

R0	R	W	0003	R16	R	W	0000	R32	R	W	0000
R1	R	W	0029	R17	R	W	0000	R33	R	W	0000
R2	R	W	4A44	R18	R	W	0000	R34	R	W	1000
R3	R	W	0000	R19	R	W	0000	R35	R	W	0640
R4	R	W	1019	R20	R	W	0028	R39	R	W	11F1
R5	R	W	0101	R21	R	W	0101	R40	R	W	101C
R6	R	W	8184	R22	R	W	8584	R41	R	W	0810
R7	R	W	1084	R23	R	W	10A4	R42	R	W	0210
R8	R	W	000A	R24	R	W	0010	R47	R	W	0000
R9	R	W	0000	R25	R	W	0000	R53	R	W	7806
R10	R	W	0000	R26	R	W	0000	R58	R	W	8C00
R11	R	W	0000	R27	R	W	0000	R60	R	W	A000
R12	R	W	0000	R28	R	W	0000				
R13	R	W	0000	R29	R	W	0000				
R14	R	W	0000	R30	R	W	0000				
R15	R	W	0000	R31	R	W	0000				

CH16