

	kHz			
	10	100	1000	10000
webench_R2=1.8k	-127	-130	-150	-152
webench_R2=6.8k	-129	-130	-150	-152
実測R2=1.8k	-119	-113	-138	-165
実測R2=6.8k	-119	-115	-138	-150
要求仕様	-120	-130	-130	-135

