




THIS DOCUMENT CONTAINS INFORMATION PROPRIETARY TO ZTE CORPORATION (ZTE). USE OR DISCLOSURE WITHOUT THE WRITTEN PERMISSION OF AN OFFICER OF ZTE IS EXPRESSLY FORBIDDEN.


SIZE-A3

DE-EMPHASIS CONTROL FOR 44.1-KHZ SAMPLING RATE:OFF(LOW)/ON(HIGH)
FILTER SELECT:NORMAL LATENCY(LOW)/LOW LATENCY(HIGH)
AUDIO FORMAT SELECTION:I2S(LOW)/LEFT-JUSTIFIED(HIGH)



I2S NEED 33 OHM SOURCE MATCHING RESISTORS

VIH(MIN)=2.31V, FOR DEMP, XSMT, FMT, LRCK, DIN, BCK, SCK, FLT



LD00 GENERATED BY THE INTERNAL LDO, RESERVED EXTERNAL 1.8V SUPPLY

ZTE CORPORATION		MODEL:	SHEET OF	
DRAWN		TITLE:	VERSION:	
CHECKED		DRAWING NO.:		