






AUDIO_PA_SDA <<>
AUDIO_PA_SCL >>
GPIO69_SPK_PDN >>


I2S_LRCK >>
I2S_SCLK >>
I2S_D0 >>
I2S_D1_1 <<






GPIO54_SPK_PWR_EN >>







Wireless Charger



Ext Hub




7 in 1 sensor Power & UART




Set to NA in Standard mode







Large cooper on SW pin



VCC 3V3: R423 3.3K --> 12K, R424 11K --> 12K 1%
 B450 --> NA, B451 --> PLACE, B452 --> PLACE
 R419 --> NA, R450 --> 0R




/OE	DIR	OPERATION
L	L	B to A
L	H	A to B
H	X	All H1-Z




DHPM_CTL_CBL >> _____
845_CTL_DHPM_PWR << _____
PHONE_ON_N << _____

To Power Key Press Board



Shipping mode Con To Bat



Power On Con To DHPM

