

EQ band	30Bands (Each Channel 15 Bands)
Output Power @4ohm, THD=1%,1KHz@12V power supply	15W
Output Power @4ohm, THD=1%,1KHz@21V Power supply	38W
THD(4 ohm load,1khz, pvdd=9v)	0.035%
Idling Current PVDD	7.8uA (Shutdown), 20.5mA (Playing with 13.2V PVDD)
Idling Current DVDD	7.4uA (Shutdown), 14.8mA (Playing with 48kHz DSP sample rate)
Efficiency @2W@4ohm@9V Vbat, 1KHz(DC)	79%
@2W@4ohm@13.2V Vbat 1KHz(DC)	72%
@4W@4ohm@9V Vbat , 1KHz(DC)	83%
@4W@4ohm@13.2V Vbat ,1KHz(DC)	79%