


ADC



S/M: 1-从模式

FMT2:FMT1:FMT0=1:0:0
音频格式 TDM, 16 000 Hz, 20 000 Hz

音频格式: TDM with One BCK Delay for Start of Frame

FS2:FS1:FS0=0:0:0
采样模式 Single Data



采样模式: Single Rate with Clock Auto-Detection

SUB: TDM子帧分配, 两芯片级联, 一高一低

SDOUT1: 通道1/2的PCM数据

SDOUT2: 通道3/4的PCM数据
对于TDM格式, SDOUT1传输

对于TDM格式, SDOUT1传输4通道的数据, SDOUT2为低



Title			
Size A2	Number		Revision
Date:	2025/9/28	Sheet	of
File:	Sheet1.SchDoc	Drawn By:	