

Analyzer

Waveform MACHINE 1

Acq. Control

Print

Run

Accumulate
On

A_CLK

X → 0

Hex

0 → 0

Center
Screen

sec/Div
50.0 us

Delay
1.132 ms

Markers
Time

X to 0
421.6 us

Trig to X
460.0 us

Trig to 0
881.6 us

A_CLK

A_CS

A_OUT

A_IN

TEST

RVS

