



Analogs	State	Volts/div	Position	Coupling	BW Limit	Invert	Probe
A1:scope1	on	1.000 V	-1.938 V	dc	off	off	1:1
A2:scope2	off	1.000 V	-2.888 V	dc	off	off	1:1

Horizontal