






USB





CV8305/ AM32001A/ ETA4662


BAT_NTC BAT_NTC_PEN

NTC


NTC



RP11 = DP SI




For Debug



$V_{out} = 0.8 * (1 + R1/R2)$

PPG_LED_5V




$V_{out} = V_{fb} * (1 + R1/R2)$

ATS3085E


File name: ATS3085E_DEBUG_V1_1_20230811.Pj.Rob	
Sheet name: POWER_SchDoc	
Drawing No:	Version: V1.0
Drawn By:	Date: 2024/9/5
Checked By:	Date:
Approved By:	Revision:
Size:	Sheet: * *

Title	
Size	Number
A4	
Date: 2024/9/5	Sheet: 1 of 1
File: E:\Hardware\POWER_SchDoc	Drawn By:





A+G Sensor




心率模组接口



PPG+ECG Sensor



固定孔



ATS3085E

File name: AT3005SE_DEMO_DPB_V1.1_20230810.LP79h	
Sheet name: SENSOR_GPS.SubDoc	
Drawing No:	Version: V1.0
Drawn By:	Date: 2024/05
Checked By:	Date:
Approved By:	Date:
Size: A3	Sheet 1 of 1