



C1	FLT[DCIM]	C2	FLT[DCIM]	C3	FLT[DCIM]	C4	FLT[DCIM]
5.00 V/div	5.00 V/div	5.00 V/div	5.00 V/div	5.00 V/div	5.00 V/div	5.00 V/div	5.00 V/div
15.000 V ofst	10.100 V ofst	3.600 V offset	-2.900 V ofst				
↓ 3.257 V	↓ 111 mV	↓ 3.420 V	↓ 3.184 V				
↑ -133 mV	↑ 3.150 V	↑ -97 mV	↑ 3.233 V				
Δy -3.391 V	Δy 3.039 V	Δy -3.517 V	Δy 49 mV				

タイムベース	-19.9 μs	トリガ	C1[DC]
	5.00 μs/div	停止	1.00 V
50.0 kS	1.0 GS/s	Edge	下向き
X1= -5.100 μs	ΔX= 49.999 μs		
X2= 44.899 μs	1/ΔX= 20.0004 kHz		