

ECG Channel (Dual - 2, Single - 1)	2	2	NA
External oscillator frequency	32768	32768	Hertz (Hz)
Main clock frequency	131072	131072	Hertz (Hz)
Time period	7.629394531	7.629394531	usec
TS# time period	244.140625	244.140625	usec
NUM_TS	16	16	Samples
RAC Period wrt NUM_TS	3906.25	3906.25	usec
COUNT_RAC	512	512	decimal
ECG Sampling rate	256	256	Hertz (Hz)
RAC Period wrt COUNT_RAC	3906.25	3906.25	usec
Decimation_Factor	0	1	NA
Decimation value	2	4	
Data Ready interrupt rate	256	256	Hertz (Hz)
Time Period single	3.90625	3.90625	millisecond (ms)
WM level	128	128	Samples
FIFO Ready period	500	1000	millisecond (ms)